

FOOT MASTER GATD-100-ASF-HUD

EAN 4031582495249

Swivel twin wheel castor, housing made of steel welded, zinc plated, double thrust bearing in the swivel head, grease nipple, tilting function to maintain contact with uneven floor, wheel axle with nut, plate fitting. Wheel centre made of cast iron, Tread: Polyurethane, casted, precision ball bearing.



BETTER MOBILITY. BETTER LIFE.



Obrázky se mohou lišit od skutečného produktu

Technické údaje

Průměr kolečka	100 mm
Šířka kola	30 mm
Šířka kolečka	131 mm
Velikost plotny	112 x 112,0 mm
Rozteč děr	92 x 92 mm
Průměr děr	9 mm
Hlava kolečka-Ø	104 mm
Vyosení	30 mm
Přesah kolečka	182 mm
Stavební výška	150 mm
Teplota	-10 / +90 °C
Hmotnost	7.01 kg
Poloměr otáčení	91 mm
Dynamická nosnost	310 kg

Vlastnosti

Valivý odpor	● ● ● ● ●
Hlučnost pohybu	● ● ● ● ○
Opotřebení	● ● ● ● ○
Ochrana proti korozi	● ● ● ● ○

Dimensions

