

OMIKRON FLEX

9850FCP200P63 83shA HL50

EAN 4031582457407



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	200 mm
Wheel width	50 mm
Size of Plate	140 x 110 mm
Plate hole centres	105 x 80 mm
Plate hole	13 mm
Centre hole	105 x 80 mm
Offset	100 mm
Swivel Interference	400 mm
Overall height	272 mm
Overall height with load	237 mm
Maximum compression	35 mm
Temperature	-20 / +60 °C
Standard	EN_12533
Weight	11 kg
Swivel Radius	200 mm
Hardness of tread	Shore A 83
Load capacity	900 kg
Load capacity (static)	1200 kg

Advantages at a glance

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○