



S10-7x25 / 8

EAN 4031582321852

threaded stem, for profile acc. to DIN 1998



Picture may differ from original product

Technical Data

Threaded stem	25 x 51 mm
Overall height	8 mm
Weight	0.023 kg
Load capacity	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○