

FAN 4031582340624

Hint: TÜV Süd certified product. Washable beds must be sealed in the fitting area by the hospital bed manufacturer.



**BETTER MOBILITY. BETTER LIFE.**



Picture may differ from original product

Wheel diameter	100 mm
Wheel width	15 mm
Castor width	60 mm
Bolt-Ø	28 mm
Bolt length	96 mm
Offset	31 mm
Swivel Interference	162 mm
Overall height	129 mm
Temperature	- 30 / + 80 °C
Standard	similar_EN12531
Weight	1.39 kg
Swivel Radius	81 mm
Hardness of tread	Shore D 40
Load capacity	125 kg
Load capacity (static)	375 kg

Technical drawing of a metal component with the following dimensions and features:

- Top view: Diameter  $\phi 100$ , radius  $R1$ , and a central slot with a width of  $\phi 28$ .
- Side view: Total height 129, base diameter  $\phi 100$ , and a central slot with a width of  $\phi 28$ .
- Front view: Total width 60, base diameter  $\phi 100$ , and a central slot with a width of  $\phi 28$ .
- Chamfer: Indicated by a triangle with a 15-degree angle and a width of 1.5.
- Other dimensions: 78.5, 96, 19, 14.8, and 11.

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

# INTEGRAL TWIN

2946USX100R26-28S45 4xM8

EAN 4031582340624



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

