

**LINEA****5947UAP125R05-28 RAL9002**

EAN 4031582369175

Swivel castor with total lock, tail end of castor, housing made of Polyamide, precision ball bearing in swivel head, solid plug fitting. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing

**TENTE**

BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

**Technical Data**

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 125 mm         |
| Wheel width            | 20 mm          |
| Castor width           | 82 mm          |
| Bolt-Ø                 | 28 mm          |
| Bolt length            | 40 mm          |
| Dome-Ø                 | 52 mm          |
| Offset                 | 40 mm          |
| Swivel Interference    | 258 mm         |
| Overall height         | 145 mm         |
| Temperature            | - 10 / + 40 °C |
| Standard               | EN_12530       |
| Weight                 | 1.076 kg       |
| Swivel Radius          | 129 mm         |
| Hardness of tread      | Shore A 92     |
| Load capacity          | 130 kg         |
| Load capacity (static) | 260 kg         |

**Advantages at a glance**

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

**Structure & Mounting**