

# STYLEA

5920UOI075L51-10 DOM20

EAN 4031582310962

Swivel castor, housing made of Polyamide, with blind hole fitting. Wheel centre made of Polyamide, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 75 mm          |
| Wheel width            | 8 mm           |
| Castor width           | 54 mm          |
| Centre hole            | 10 mm          |
| Dome-Ø                 | 20 mm          |
| Offset                 | 30 mm          |
| Swivel Interference    | 124 mm         |
| Overall height         | 77 mm          |
| Temperature            | - 20 / + 60 °C |
| Standard               | EN_12528       |
| Weight                 | 0.119 kg       |
| Swivel Radius          | 62 mm          |
| Hardness of tread      | Shore D 65     |
| Load capacity          | 50 kg          |
| Load capacity (static) | 100 kg         |

## Structure & Mounting



## Advantages at a glance

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |