

## P11-40x17 / 8

EAN 4031582320176

stem with L-shaped plate



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

### Technical Data

Size of Plate	40 x 17 mm
Plate hole centres	32 mm
Plate hole	4 mm
Overall height	8 mm
Load capacity	40 kg
Load capacity (static)	80 kg

### Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○