

S73-10x78 / 10

EAN 4031582321975

threaded stem with round neck, riveted



Picture may differ from original product

Technical Data

Threaded stem	M 10 x 78 mm
Overall height	9 mm
Weight	0.052 kg
Load capacity	80 kg
Load capacity (static)	160 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○