

EAN 4031582340624

Hint: TÜV Süd certified product. Washable beds must be sealed in the fitting area by the hospital bed manufacturer.



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Wheel diameter	100 mm
Wheel width	15 mm
Castor width	60 mm
Bolt-Ø	28 mm
Bolt length	96 mm
Offset	31 mm
Swivel Interference	162 mm
Overall height	129 mm
Temperature	- 30 / + 80 °C
Standard	similar_EN12531
Weight	1.39 kg
Swivel Radius	81 mm
Hardness of tread	Shore D 40
Load capacity	125 kg
Load capacity (static)	375 kg

Technical drawing of a cylindrical component with the following dimensions and features:

- Top view: Diameter $\phi 100$, radius $\phi 31$.
- Front view: Total height 129, top flange diameter $\phi 28$, flange thickness 11, main body diameter $\phi 78.5$, main body height 96, bottom flange diameter $\phi 19$, bottom flange thickness 8.
- Side view: Chamfer angle 45° , chamfer width 15.
- Text: S45 = Schaltwinkel 2x 45°

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

INTEGRAL TWIN

2946USX100R26-28S45 4xM8

EAN 4031582340624



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

