

**LINEA****5945UAP050L51-8 7011**

EAN 4031582430226

Swivel castor with wheel brake, housing made of Polyamide, precision ball bearing in swivel head, with blind hole fitting. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing



BETTER MOBILITY. BETTER LIFE.





Picture may differ from original product

**Technical Data**

Wheel diameter	50 mm
Wheel width	13 mm
Castor width	47.5 mm
Centre hole	8 mm
Dome-Ø	23 mm
Swivel Interference	102 mm
Overall height	50 mm
Temperature	- 10 / + 40 °C
Standard	EN_12530
Weight	0.092 kg
Swivel Radius	51 mm
Hardness of tread	Shore A 92
Load capacity	100 kg
Load capacity (static)	200 kg

**Advantages at a glance**

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

**Dimensions****Structure & Mounting**

# LINEA

5945UAP050L51-8 7011

EAN 4031582430226



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

