

AGILA

2670JP3.5x1.25P52-95x70

EAN 4031582434651

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	88.9 mm
Wheel width	31.75 mm
Size of Plate	95 x 70 mm
Plate hole centres	44,45 x 76,2 mm
Plate hole	11 mm
Offset	34 mm
Swivel Interference	157 mm
Axle Hole-Ø	10 mm
Hub length	41 mm
Overall height	116.7 mm
Standard	ICWM
Swivel Radius	78.5 mm
Hardness of tread	Shore A 77
Load capacity	95 kg
Load capacity (static)	190 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

AGILA

2670PJP3.5x1.25P52-95x70

EAN 4031582434651



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

