

# AGILA

267FPJO3.5x1.25P52-95x70

EAN 4031582435160

Swivel castor with Butterfly wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

|                        |                 |
|------------------------|-----------------|
| Wheel diameter         | 88.9 mm         |
| Wheel width            | 31.75 mm        |
| Size of Plate          | 95 x 70 mm      |
| Plate hole centres     | 44,45 x 76,2 mm |
| Plate hole             | 11 mm           |
| Offset                 | 34 mm           |
| Swivel Interference    | 157 mm          |
| Axle Hole-Ø            | 10 mm           |
| Hub length             | 41 mm           |
| Overall height         | 116.7 mm        |
| Standard               | ICWM            |
| Swivel Radius          | 78.5 mm         |
| Hardness of tread      | Shore A 77      |
| Load capacity          | 95 kg           |
| Load capacity (static) | 190 kg          |

## Advantages at a glance

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

# AGILA

267FPJO3.5x1.25P52-95x70

EAN 4031582435160



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

