

AGILA

2675POO5x1.25P52-95x70

EAN 4031582435863

Swivel castor with wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel centre made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

| | |
|------------------------|-----------------|
| Wheel diameter | 127 mm |
| Wheel width | 31.75 mm |
| Size of Plate | 95 x 70 mm |
| Plate hole centres | 44,45 x 76,2 mm |
| Plate hole | 11 mm |
| Offset | 37 mm |
| Swivel Interference | 237 mm |
| Axle Hole-Ø | 10 mm |
| Hub length | 41 mm |
| Overall height | 159 mm |
| Standard | ICWM |
| Swivel Radius | 118.5 mm |
| Hardness of tread | Shore D 66 |
| Load capacity | 150 kg |
| Load capacity (static) | 300 kg |

Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

AGILA

2675POO5x1.25P52-95x70

EAN 4031582435863



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

