

# AGILA

2677PJO5x1.25P52-95x70

EAN 4031582435924

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head  
Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

Wheel diameter	127 mm
Wheel width	31.75 mm
Size of Plate	95 x 70 mm
Plate hole centres	44,45 x 76,2 mm
Plate hole	11 mm
Offset	37 mm
Swivel Interference	237 mm
Axle Hole-Ø	10 mm
Hub length	41 mm
Overall height	159 mm
Standard	ICWM
Swivel Radius	118.5 mm
Hardness of tread	Shore A 77
Load capacity	125 kg
Load capacity (static)	250 kg

## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

# AGILA

2677PJO5x1.25P52-95x70

EAN 4031582435924



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

