

S70-10x25 / 8

EAN 4031582321920

threaded stem with hexagon neck



Picture may differ from original product

Technical Data

Threaded stem	M 10 x 25 mm
Overall height	6 mm
Weight	0.027 kg
Load capacity	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○