

LUMINA

A525POI050P41 TFR

EAN 4031582395327

Swivel castor with wheel brake, housing made of Polypropylene, plate fitting. Wheel centre made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	50 mm
Wheel width	7 mm
Castor width	54 mm
Size of Plate	38 x 38 mm
Swivel Interference	124 mm
Overall height	56 mm
Temperature	- 10 / + 40 °C
Standard	EN_12528
Weight	0.056 kg
Swivel Radius	62 mm
Hardness of tread	Shore D 65
Load capacity	40 kg
Load capacity (static)	80 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○