

LINEA

5984UAP150R36-32S30

EAN 4031582382518

Swivel castor with central, total lock and central directional lock, housing made of Polyamide, precision ball bearing in swivel head, stem with cam hole for profile bars, short version. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

| | |
|------------------------|----------------|
| Wheel diameter | 150 mm |
| Wheel width | 15 mm |
| Castor width | 71 mm |
| Bolt-Ø | 32 mm |
| Bolt length | 51 mm |
| Dome-Ø | 46 mm |
| Offset | 47.5 mm |
| Swivel Interference | 245 mm |
| Overall height | 155 mm |
| Temperature | - 10 / + 40 °C |
| Standard | EN_12530 |
| Weight | 1.624 kg |
| Swivel Radius | 122.5 mm |
| Hardness of tread | Shore D 42 |
| Load capacity | 200 kg |
| Load capacity (static) | 400 kg |

Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |