

STORA

3875ZJJ160P30-13 LEFT

EAN 4031582328554

Walkway Castor with automatic side brake for moving walkways, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, flanged wheel with one ball race, left and right hand design, wheel axle with nut, Wheel centre made of plastic, Tread: TENTEprene (thermoplastic rubber), with threadguards, roller bearing. Designed for the following palletsize: track width: approx: 2,75 mm, groove width: approx. 5,7 mm, groove depth: > 10 mm.

Hint:

Load capacity 160 kg per castor on level and securely attached floors, 40 kg per castor on walkways. Use on uneven floors, outdoors (ground beams, gaps, joints, manhole covers, etc.) can affect the life expectancy of castors.



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product


Technical Data

| | |
|------------------------|----------------|
| Wheel diameter | 160 mm |
| Wheel width | 40 mm |
| Castor width | 96 mm |
| Centre hole | 13 mm |
| Dome-Ø | 96 mm |
| Offset | 55 mm |
| Swivel Interference | 270 mm |
| Overall height | 186 mm |
| Temperature | - 20 / + 60 °C |
| Standard | EN_12532 |
| Weight | 1.899 kg |
| Swivel Radius | 135 mm |
| Hardness of tread | Shore A 87 |
| Load capacity | 160 kg |
| Load capacity (static) | 320 kg |


Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

Dimensions



Structure & Mounting



STORA

3875ZJJ160P30-13 LEFT

EAN 4031582328554



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

