

# BASETECH

PQR260x85-Ø20 HL74 4PR

EAN 4031582321050

Wheel centre made of Polypropylene, Tread: pneumatic tyre, roller bearing, block profile



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

## Technical Data

Wheel diameter	260 mm
Wheel width	85 mm
Axle Hole-Ø	20 mm
Hub length	74 mm
Temperature	- 20 / + 60 °C
Standard	EN_12532
Weight	1.07 kg
Hardness of tread	Shore A 55
Load capacity	75 kg
Load capacity (static)	150 kg

## Dimensions



## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○