

AVIANA

5979PIP075R36-32S30

EAN 4031582382761

Swivel castor with central total lock, housing made from high grade synthetic materials, double ball bearing swivel head, axle riveted, stem with cam hole for profile bars, short version. Wheel centre made of Polypropylene, Tread: solid rubber, grey non-marking, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	75 mm
Wheel width	25 mm
Castor width	69 mm
Bolt-Ø	32 mm
Bolt length	51 mm
Dome-Ø	54 mm
Offset	29 mm
Swivel Interference	138 mm
Overall height	104.5 mm
Temperature	- 10 / + 40 °C
Standard	EN_12530
Weight	0.688 kg
Swivel Radius	69.5 mm
Hardness of tread	Shore A 80
Load capacity	100 kg
Load capacity (static)	200 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○