

P10-40x17 / 8

EAN 4031582320114

stem with U-shaped plate



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

| | |
|------------------------|------------|
| Size of Plate | 40 x 17 mm |
| Plate hole centres | 32 mm |
| Plate hole | 4 mm |
| Overall height | 8 mm |
| Weight | 0.042 kg |
| Load capacity | 40 kg |
| Load capacity (static) | 80 kg |

Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ○ ○ ○ ○ ○ |
| Movement noise | ○ ○ ○ ○ ○ |
| Attrition | ○ ○ ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |