

# E-DRIVE FLEX


EDFAUFF125P60

EAN 4031582416664

E-Drive flex, Drive unit can be lowered and raised, Solid housing made of galvanized sheet steel, the wheel can be replaced by the customer and ordered individually, maintenance-free



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product


## Technical Data

Wheel	UFF, solid rubber, non-marking, Shore 63A
Wheel size	125 mm
Wheel width	35 mm
Installation height	170 mm
Length	max. 315 mm (emergency release actuated)
Emergency release	Mechanical
Width	190 mm
Drive motor	24 V DC
Driving directions	forward / backward
Height (folded)	140 mm
Floor compensation	+/- 30 mm
Max. height of threshold that can be crossed	15 mm
Max. Lifting force / contact pressure	400 N
Weight	6 kg

## Drive motor

Nominal voltage	24 V DC
Nominal torque	4 Nm
Nominal power	73.1 W
Nominal RPM	174.50 min/-1
Nominal voltage	7.0 A

## Dimensions



# E-DRIVE FLEX

EDFAUFF125P60

EAN 4031582416664



BETTER MOBILITY. BETTER LIFE.

Operating mode	S1 + S4
Max. Speed	4 km/h

## Actuator

Nominal voltage	24 V DC
Nominal torque	4 Nm
Nominal power	14.8 W
Nominal RPM	35.3 min/-1
Nominal voltage	3.5 A
Operating mode	periodic S3
Permitted environmental conditions	operating temperature 5 to 50° C (recommend 15 to 50° C) , atmospheric humidity 90%, non-condensing
Permitted storage temperatures	-10 bis 36° C
Protection class	IP X4 (splash water from all sides, all plugs connected)

## Advantages at a glance

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○