



BETTER MOBILITY. BETTER LIFE.

S70-10x15 / 10

EAN 4031582321876

threaded stem with hexagon neck



Picture may differ from original product

Technical Data

Threaded stem	M 10 x 15 mm
Overall height	6 mm
Weight	0.025 kg
Load capacity	80 kg
Load capacity (static)	160 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○