

# E-DRIVE ULTIMATE

EDUZ110

EAN 4031582478341

E-Drive ultimate Control unit 24V single Control, E-Drive with 24V drive, control unit 24 V without battery cables



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

## Technical Data

Required power supply	24 V DC
Cable routing	flexible to the components, Plug & Play
Cable length	3 m to the drive unit
Updates	Network interface for firmware and parameter updates
Assembly	individual assembly through integrated mounting plate
Dimensions	see drawing
Weight	2.7 kg
Current consumption	16 A
Reverse polarity protection	integrated in connections
Protection class	IP X4 (splash water from all sides, all plugs connected)
Permissible operating temperature	operating temperature 5 to 50° C (recommend 15 to 50° C), atmospheric humidity 90%, non-condensing
Permitted storage temperatures	- 20 to 45° C

## Dimensions



## Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○