

LINEA**5940UAP125R05-28 RAL9002**

EAN 4031582347371

Swivel castor, housing made of Polyamide, precision ball bearing in swivel head, solid plug fitting. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing

TENTE

BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

Technical Data

Wheel diameter	125 mm
Wheel width	20 mm
Castor width	82 mm
Bolt-Ø	28 mm
Bolt length	40 mm
Dome-Ø	52 mm
Offset	40 mm
Swivel Interference	218 mm
Overall height	143 mm
Temperature	- 20 / + 60 °C
Standard	EN_12530
Weight	0.962 kg
Swivel Radius	109 mm
Hardness of tread	Shore A 92
Load capacity	110 kg
Load capacity (static)	220 kg

Advantages at a glance

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

Dimensions**Structure & Mounting**