

# OMIKRON FLEX

9850FCP200P63-75shA HL50

EAN 4031582479089

Swivel castor, plate fitting. Wheel centre made of cast iron, Tread: Polyurethane, casted, Ultratech, suitable especially for higher speeds of up to 16 km/h, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

|                          |              |
|--------------------------|--------------|
| Wheel diameter           | 200 mm       |
| Wheel width              | 50 mm        |
| Size of Plate            | 140 x 110 mm |
| Plate hole centres       | 105 x 80 mm  |
| Plate hole               | 13 mm        |
| Centre hole              | 105 x 80 mm  |
| Offset                   | 100 mm       |
| Swivel Interference      | 400 mm       |
| Overall height           | 272 mm       |
| Overall height with load | 237 mm       |
| Maximum compression      | 35 mm        |
| Temperature              | -20 / +60 °C |
| Standard                 | EN_12533     |
| Weight                   | 11 kg        |
| Swivel Radius            | 200 mm       |
| Hardness of tread        | Shore A 75   |
| Load capacity            | 900 kg       |
| Load capacity (static)   | 1200 kg      |

## Advantages at a glance

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |