

# ULTRATECH

ICP160x50-Ø20 soft

EAN 4031582445084

Wheel centre made of Aluminium, Tread: Polyurethane, casted, Ultratech, suitable especially for higher speeds of up to 16 km/h, precision ball bearing



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

## Technical Data

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 160 mm         |
| Wheel width            | 50 mm          |
| Axle Hole-Ø            | 20 mm          |
| Hub length             | 60 mm          |
| Temperature            | - 20 / + 60 °C |
| Standard               | EN_12532       |
| Weight                 | 1.1 kg         |
| Hardness of tread      | Shore A 75     |
| Load capacity          | 800 kg         |
| Load capacity (static) | 1600 kg        |

## Dimensions



## Advantages at a glance

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## Structure & Mounting

