

OMIKRON FLEX

9850ICP160P63-92A HL50

EAN 4031582479058

Swivel castor, plate fitting. Wheel centre made of Aluminium, Tread: Polyurethane, casted, Ultratech, suitable especially for higher speeds of up to 16 km/h, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	160 mm
Wheel width	50 mm
Size of Plate	140 x 110 mm
Plate hole centres	105 x 80 mm
Plate hole	20 x 13 mm
Offset	100 mm
Swivel Interference	360 mm
Overall height	252 mm
Overall height with load	217 mm
Maximum compression	35 mm
Temperature	-20 / +60 °C
Standard	EN_12533
Weight	9 kg
Swivel Radius	200 mm
Hardness of tread	Shore A 92
Load capacity	900 kg
Load capacity (static)	1200 kg

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○