

# DELTA

## 3648IEP125P63

EAN 4031582337174

Fixed castor, Fork made of heavy pressed steel, bright zinc plated, blue passivated, wheel axle with nut, plate fitting.

Wheel centre made of Aluminium, Tread: black elastic-tyre, vulcanized, precision ball bearing



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

### Technical Data

Wheel diameter	125 mm
Wheel width	50 mm
Castor width	115 mm
Size of Plate	137 x 115,0 mm
Plate hole centres	105 x 80/75 mm
Plate hole	11 mm
Dome-Ø	115 mm
Overall height	178 mm
Temperature	- 20 / + 85 °C
Standard	EN_12532
Weight	1.83 kg
Hardness of tread	Shore A 68
Load capacity	300 kg
Load capacity (static)	600 kg

### Dimensions



### Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

# DELTA

3648IEP125P63

EAN 4031582337174



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

