

AGILA

2675POO5x1.25P52-95x70

EAN 4031582435863

Swivel castor with wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel centre made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	127 mm
Wheel width	31.75 mm
Size of Plate	95 x 70 mm
Plate hole centres	44,45 x 76,2 mm
Plate hole	11 mm
Offset	37 mm
Swivel Interference	237 mm
Axle Hole-Ø	10 mm
Hub length	41 mm
Overall height	159 mm
Standard	ICWM
Swivel Radius	118.5 mm
Hardness of tread	Shore D 66
Load capacity	150 kg
Load capacity (static)	300 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

AGILA

2675POO5x1.25P52-95x70

EAN 4031582435863



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

