

KAPPA FLEX

9758ITP200P63 SH92A

EAN 4031582443646

Fixed castor, With spring, Housing and plate steel-welded, heavy duty, plate fitting.
 Wheel centre made of Aluminium, Tread: Polyurethane, casted, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	200 mm
Wheel width	50 mm
Size of Plate	142 x 111 mm
Plate hole centres	112/99 x 83/74 mm
Plate hole	12.7 mm
Overall height	260 mm
Temperature	-20 / +60 °C
Standard	EN_12533
Weight	4.7 kg
Hardness of tread	Shore A 92
Load capacity	450 kg
Load capacity (static)	600 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	○ ○ ○ ○ ○