

# NOVATECH

## ETP080x25-Ø20 HL14

EAN 4031582318531

Wheel centre made of steel, Tread: Polyurethane, casted, precision ball bearing.

Load capacities on a smooth, even surface.



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

### Technical Data

Wheel diameter	80 mm
Wheel width	25 mm
Axle Hole-Ø	20 mm
Hub length	14 mm
Temperature	- 10 / + 60 °C
Standard	EN_12532
Weight	0.38 kg
Hardness of tread	Shore A 92
Load capacity	160 kg
Load capacity (static)	320 kg

### Dimensions



### Advantages at a glance

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

### Structure & Mounting

