

ALPHA

3477PVR100P62

EAN 4031582050714

Swivel castor with total lock, tail end of castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, dustguard, plate fitting. Wheel centre made of Polypropylene, Tread: solid rubber, black, roller bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

| | |
|------------------------|----------------|
| Wheel diameter | 100 mm |
| Wheel width | 35 mm |
| Castor width | 75 mm |
| Size of Plate | 105 x 80 mm |
| Plate hole centres | 80/77 x 60 mm |
| Plate hole | 9 mm |
| Dome-Ø | 75 mm |
| Offset | 41 mm |
| Swivel Interference | 246 mm |
| Overall height | 128 mm |
| Temperature | - 20 / + 60 °C |
| Standard | EN_12532 |
| Weight | 0.959 kg |
| Swivel Radius | 123 mm |
| Hardness of tread | Shore A 80 |
| Load capacity | 75 kg |
| Load capacity (static) | 150 kg |

Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

Dimensions



Structure & Mounting



ALPHA

3477PVR100P62

EAN 4031582050714



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

