

SCOUT

8148UFC200P60 smart

EAN 4031582429886

Fixed castor, stainless steel housing, plate fittingFixed castor, plate fitting.
Wheel centre made of polyamide, tread made of a non-marking elastic
tyre, with small thread guard, two INOX precision ball bearings, sealed,
washable



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	200 mm
Wheel width	40 mm
Castor width	72 mm
Size of Plate	130 x 74 mm
Plate hole centres	110 x 50 mm
Plate hole	10,5 mm
Overall height	242 mm
Temperature	-20 / +80 °C
Weight	2.295 kg
Hardness of tread	Shore A 64
Load capacity	150 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

SCOUT

8148UFC200P60 smart

EAN 4031582429886



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

