

P11-40x25 / 8

EAN 4031582320206

stem with L-shaped plate



Picture may differ from original product

Technical Data

|                        |            |
|------------------------|------------|
| Size of Plate          | 40 x 25 mm |
| Plate hole centres     | 32 mm      |
| Plate hole             | 4 mm       |
| Overall height         | 8 mm       |
| Load capacity          | 40 kg      |
| Load capacity (static) | 80 kg      |

Advantages at a glance

|                      |           |
|----------------------|-----------|
| Roll performance     | ○ ○ ○ ○ ○ |
| Movement noise       | ○ ○ ○ ○ ○ |
| Attrition            | ○ ○ ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |