

S70-10x25 / 8

EAN 4031582321920

threaded stem with hexagon neck



Picture may differ from original product

Technical Data

| | |
|------------------------|--------------|
| Threaded stem | M 10 x 25 mm |
| Overall height | 6 mm |
| Weight | 0.027 kg |
| Load capacity | 40 kg |
| Load capacity (static) | 80 kg |

Advantages at a glance

| | |
|----------------------|-----------|
| Roll performance | ○ ○ ○ ○ ○ |
| Movement noise | ○ ○ ○ ○ ○ |
| Attrition | ○ ○ ○ ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |