

# PURETECH

PIO075x25-Ø8

EAN 4031582356632

Wheel centre made of Polypropylene, Tread: solid rubber, grey non-marking, plain bearing



Picture may differ from original product

### Technical Data

Wheel diameter	75 mm
Wheel width	25 mm
Axle Hole-Ø	8 mm
Hub length	26.5 mm
Temperature	- 20 / + 60 °C
Standard	EN_12530
Weight	0.1 kg
Hardness of tread	Shore A 87
Load capacity	60 kg
Load capacity (static)	120 kg

### Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○