

FAN 4031582368468

Hint: These castors are also with grey locking lever available.



BETTER MOBILITY. BETTER LIFE.




Technical Data

Wheel diameter	100 mm
Wheel width	30 mm
Bolt-Ø	28 mm
Bolt length	40 mm
Offset	40 mm
Swivel Interference	205 mm
Overall height	139 mm
Temperature	-20 / +60 °C
Standard	EN_12530
Hardness of tread	Shore A 87
Load capacity	100 kg
Load capacity (static)	200 kg

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

Dimensions



Structure & Mounting

