

COMPACTA

2198PJI032P60-45,5X20

EAN 4031582418590

Fixed castor, Fork made of pressed steel, bright zinc plated, blue passivated, axle riveted, plate fitting.

Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	32 mm
Wheel width	15 mm
Castor width	20 mm
Size of Plate	45 x 20 mm
Plate hole centres	34.8 mm
Plate hole	5,5 mm
Overall height	34 mm
Temperature	- 20 / + 60 °C
Standard	EN_12528
Weight	0.031 kg
Hardness of tread	Shore A 87
Load capacity	30 kg
Load capacity (static)	60 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○