

STYLEA

5925UOI075S70-10X15 TFR

EAN 4031582385687

Swivel castor with wheel brake, housing made of Polyamide, threaded stem with hexagon neck. Wheel centre made of Polyamide, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	75 mm
Wheel width	8 mm
Castor width	54 mm
Threaded stem	10 x 15 mm
Swivel Interference	174 mm
Overall height	88 mm
Temperature	- 10 / + 40 °C
Standard	EN_12528
Weight	0.157 kg
Swivel Radius	87 mm
Hardness of tread	Shore D 75
Load capacity	50 kg
Load capacity (static)	100 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○