

# ANIKA

5920UAI065L51-10 DOM18 9011-7015

EAN 4031582437003

Swivel castor, housing made of Polyamide, with blind hole fitting. Wheel centre made of Polyamide, Tread: Polyurethane, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

|                        |                |
|------------------------|----------------|
| Wheel diameter         | 65 mm          |
| Wheel width            | 11 mm          |
| Castor width           | 39.5 mm        |
| Centre hole            | 10 mm          |
| Dome-Ø                 | 18 mm          |
| Swivel Interference    | 111 mm         |
| Overall height         | 67 mm          |
| Temperature            | - 10 / + 40 °C |
| Standard               | EN_12528       |
| Weight                 | 0.075 kg       |
| Swivel Radius          | 55.5 mm        |
| Hardness of tread      | Shore A 92     |
| Load capacity          | 50 kg          |
| Load capacity (static) | 100 kg         |

## Structure & Mounting



## Advantages at a glance

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |