

COMPACTA

1530POO040P41

EAN 4031582429220

Swivel caster, Steel semi-spherical holes stamped, bright zinc plated. Single ball race swivel head, axle riveted, plate fitting. Wheel center made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	1.26 in
Plate size	1.38 x 1.38 in
Plate hole centers	0.98 x 0.98 in
Plate hole	0.20 in
Offset	0.67 in
Swivel Interference	2.91 in
Overall height	2.09 in
Temperature	- 4 / + 140 °F
Standard	EN 12528
Weight	0.220 lbs
Swivel Radius	1.46 in
Hardness of tread	Shore A 95
Load capacity (dynamic)	90 lbs
Load capacity (static)	175 lbs

Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○