

AGILA

2678POO3.5x1.25P52-95x70

EAN 4031582434699

Fixed caster, Fork made of pressed steel, bright zinc plated, blue passivated
Wheel center made of Polypropylene, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	3.5 in
Wheel width	1.25 in
Plate size	3.74 x 2.76 in
Plate hole centers	1.75 x 3.00 in
Plate hole	0.43 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	4.59 in
Standard	ICWM
Hardness of tread	Shore D 66
Load capacity (dynamic)	275 lbs
Load capacity (static)	550 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

AGILA

2678POO3.5x1.25P52-95x70

EAN 4031582434699



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

