

# AGILA

267FPAP3x1.25P30-13

EAN 4031582435290

Swivel castor with Butterfly wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, Tread: Polyurethane, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

Wheel diameter	3 in
Wheel width	1.25 in
Center hole	0.51 in
Offset	1.42 in
Swivel Interference	5.83 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	3.98 in
Standard	ICWM
Swivel Radius	2.92 in
Hardness of tread	Shore D 41
Load capacity (dynamic)	225 lbs
Load capacity (static)	450 lbs

## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

# AGILA

267FPAP3x1.25P30-13

EAN 4031582435290



BETTER MOBILITY. BETTER LIFE.

## Structure & Mounting

---

