

AGILA

267FPJP4x1.25P30-13

EAN 4031582435351

Swivel castor with Butterfly wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head Wheel center made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	4 in
Wheel width	1.25 in
Center hole	0.51 in
Offset	1.50 in
Swivel Interference	6.93 in
Axle Hole-Ø	0.39 in
Hub length	1.61 in
Overall height	5.00 in
Standard	ICWM
Swivel Radius	3.50 in
Hardness of tread	Shore A 77
Load capacity (dynamic)	250 lbs
Load capacity (static)	500 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	○ ○ ○ ○ ○

AGILA

267FPJP4x1.25P30-13

EAN 4031582435351



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

