

FORMA

6944UFP150P33 Q1-L30 white

EAN 4031582476354

Swivel Caster with central, total or directional lock, housing made of alu die-casting, powder coated, plate fitting. Wheel center made of Polyamide, Tread: elastic-tire, non-marking, precision ball bearing



Picture may differ from original product

Technical Data

Wheel diameter	5.91 in
Wheel width	0.71 in
Plate size	3.62 x 2.52 in
Plate hole centers	2.87 x 1.69 in
Plate hole	0.35 in
Offset	2.24 in
Overall height	8.15 in
Temperature	- 0 / + 248 °F
Swivel Radius	5.39 in
Hardness of tread	Shore 60 A
Load capacity (dynamic)	300 lbs

Advantages at a glance

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

FORMA

6944UFP150P33 Q1-L30 white

EAN 4031582476354



BETTER MOBILITY. BETTER LIFE.

Structure & Mounting

