

STYLEA

5925UOI075L51-10 DOM20

EAN 4031582311242



BETTER MOBILITY. BETTER LIFE.

Swivel caster with wheel brake, housing made of Polyamide, with blind hole fitting. Wheel center made of Polyamide, plain bearing




Picture may differ from original product

Technical Data

Wheel diameter	2.95 in
Wheel width	0.31 in
Caster width	2.13 in
Center hole	0.39 in
Dome-Ø	0.79 in
Offset	1.18 in
Swivel Interference	6.85 in
Overall height	3.03 in
Temperature	- 4 / + 140 °F
Standard	EN 12528
Weight	0.284 lbs
Swivel Radius	3.43 in
Hardness of tread	Shore D 65
Load capacity (dynamic)	110 lbs
Load capacity (static)	220 lbs

Structure & Mounting



Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○