



BETTER MOBILITY. BETTER LIFE.

## S70-10x15 / 10

EAN 4031582321876

threaded stem with hex neck



Picture may differ from original product

### Technical Data

Threaded stem	M 10 x 15 mm
Overall height	0.24 in
Weight	0.055 lbs
Load capacity (dynamic)	175 lbs
Load capacity (static)	355 lbs

### Advantages at a glance

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	● ● ● ○ ○