

AGILA

1470PAO050P30-11

EAN 4031582338461

Swivel caster, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole. Wheel center made of Polypropylene, Tread: Polyurethane, plain bearing



Picture may differ from original product

Technical Data

Wheel diameter	1.97 in
Wheel width	0.75 in
Caster width	1.73 in
Center hole	0.43 in
Dome-Ø	1.61 in
Offset	0.98 in
Swivel Interference	3.94 in
Overall height	2.76 in
Temperature	- 4 / + 140 °F
Standard	EN 12530
Weight	0.353 lbs
Swivel Radius	1.97 in
Hardness of tread	Shore D 40
Load capacity (dynamic)	90 lbs
Load capacity (static)	175 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○