

AGILA

1470PAO050P30-11

EAN 4031582338461

Swivel caster, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole. Wheel center made of Polypropylene, Tread: Polyurethane, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	1.97 in
Wheel width	0.75 in
Caster width	1.73 in
Center hole	0.43 in
Dome-Ø	1.61 in
Offset	0.98 in
Swivel Interference	3.94 in
Overall height	2.76 in
Temperature	- 4 / + 140 °F
Standard	EN 12530
Weight	0.353 lbs
Swivel Radius	1.97 in
Hardness of tread	Shore D 40
Load capacity (dynamic)	90 lbs
Load capacity (static)	175 lbs

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○